



T8 Standard

F30T8/CW ALTO 30PK

Philips T8 lamps are energy-efficient lighting solutions.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Light Technical	
Color Code	TL841 [CCT of 4100K (841)]
Luminous Flux	2,200 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	>60
Operating and Electrical	
Power Consumption	30 W
Lamp Current (Nom)	355 A
Wattage Equivalent	30 W
Voltage (Nom)	99 V
Mechanical and Housing	
Bulb Finish	Coated glass

Bulb Shape	T-8
Net Weight (Piece)	0.102 kg
Approval and Application	
Mercury (Hg) Content (Max)	1.9 mg
Mercury (Hg) Content (Nom)	1.5 mg
Product Data	
Order product name	F30T8/CW ALTO 30PK
Full product name	F30T8/CW ALTO 30PK
Order code	927825503311
Material Nr. (12NC)	927825503311
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677571030
Numerator - Packs per outer box	30
EAN/UPC - Case	50046677571035

T8 Standard

Dimensional drawing

Product

F30T8/CW ALTO 30PK

