



MASTER TL-D Super 80

TLDRS16W-S84ECO 25PK

The MASTER TL-D Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	8,000 hour(s)

Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	1,200 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	85

Operating and Electrical	
Power Consumption	16 W
Lamp Current (Nom)	0.265 A

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T8
Net Weight (Piece)	70.800 g

Approval and Application	
Mercury (Hg) Content (Nom)	3.0 mg
Energy Consumption kWh/1000 h	20 kWh

Product Data	
Order product name	TLDRS16W-S84ECO 25PK
Full product name	TLDRS16W-S84ECO 25PK
Full product code	872790091769700
Order code	927850074102
Material Nr. (12NC)	927850074102

MASTER TL-D Super 80

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900917697
Numerator - Packs per outer box	25

EAN/UPC - Case	8727900917703
----------------	---------------

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TLDRS16W-S84ECO 25PK	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

