



MASTER TL-D Super 80

TLDRS16W-S85ECO 25PK

The MASTER TL-D Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Net Weight (Piece)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		70.800 g
Features	ALTO® (ALTO)	Approval and Application	
Light Technical		Energy Saving Product	Energy Saving
Color Code	TL850 [CCT of 5000K (850)]	Mercury (Hg) Content (Nom)	1.7 mg
Luminous Flux	1,300 lm	Product Data	
Color Designation	TL850	Order product name	TLDRS16W-S85ECO 25PK
Correlated Color Temperature (Nom)	5000 K	Full product name	TLDRS16W-S85ECO 25PK
Color rendering index (CRI)	82	Full product code	872790091771000
Operating and Electrical		Order code	927850085002
Power Consumption	17 W	Material Nr. (12NC)	927850085002
Mechanical and Housing		Numerator - Quantity Per Pack	1
Bulb Shape	T-8	EAN/UPC - Product/Case	8727900917710
		Numerator - Packs per outer box	25
		EAN/UPC - Case	8727900917727

MASTER TL-D Super 80

Dimensional drawing

Product

TLDRS16W-S85ECO 25PK

