



# MASTER TL-D Super 80

## TLDRS16W-S85ECO 25PK

The MASTER TL-D Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Light Technical	
Color Code	TL850 [CCT of 5000K (850)]
Luminous Flux	1,300 lm
Color Designation	TL850
Correlated Color Temperature (Nom)	5000 K
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	17 W
Mechanical and Housing	
Bulb Shape	T-8

Net Weight (Piece)	70.800 g
Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	1.7 mg
Product Data	
Order product name	TLDRS16W-S85ECO 25PK
Full product name	TLDRS16W-S85ECO 25PK
Full product code	872790091771000
Order code	927850085002
Material Nr. (12NC)	927850085002
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900917710
Numerator - Packs per outer box	25
EAN/UPC - Case	8727900917727

# MASTER TL-D Super 80

---

## Dimensional drawing

### Product

TLDRS16W-S85ECO 25PK

