



# U-Bent Energy Advantage T8

## FB32T8/ADV850/6/XEW/ALTO 25W

Philips Energy Advantage T8 25W U-Bent Lamps are environmentally responsible lamps, featuring energy savings and low mercury.

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)

  

Light Technical	
Color Code	Advantage 850 [CCT of 5000K]
Luminous Flux	2,350 lm
Color Designation	Advantage 850
Correlated Color Temperature (Nom)	5000 K
Color rendering index (CRI)	85

  

Operating and Electrical	
Power Consumption	25 W

  

Mechanical and Housing	
Bulb Shape	T8-6U [U-bent T 8/8 inch with 6" spacing]
Net Weight (Piece)	0.001 kg

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	3.0 mg

  

Product Data	
Order product name	FB32T8/ADV850/6/XEW/ALTO 25W
Full product name	FB32T8/ADV850/6/XEW/ALTO 25W
Order code	927860185101
Material Nr. (12NC)	927860185101
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677204242
Numerator - Packs per outer box	20
EAN/UPC - Case	50046677204247

# U-Bent Energy Advantage T8

## Dimensional drawing

### Product

FB32T8/ADV850/6/XEW/ALTO 25W

