



U-Bent Rapid Start T8

FB31T8/TL841/ALTO 15/1

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Light Technical	
Color Code	TL841 [CCT of 4100K (841)]
Luminous Flux	2,750 lm
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	85
Operating and Electrical	
Power Consumption	31 W
Mechanical and Housing	
Bulb Shape	T8-1-5/8U [U-bent T 1inch with 1-5/8" leg spacing]
Net Weight (Piece)	0.001 kg

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	3.0 mg
Product Data	
Order product name	FB31T8/TL841/ALTO 15/1
Full product name	FB31T8/TL841/ALTO 15/1
Order code	927861284101
Material Nr. (12NC)	927861284101
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677226749
Numerator - Packs per outer box	15
EAN/UPC - Case	50046677226744

U-Bent Rapid Start T8

Dimensional drawing

Product

FB31T8/TL841/ALTO 15/1

