



# U-Bent Rapid Start T12

## FB40DX/6 12PK

Philips T12 fluorescent lamps provide high performance and long life in a wide range of sizes, shapes, and types.

### Product data

General Information		Approval and Application	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Energy Saving Product	Not Applicable
		Mercury (Hg) Content (Nom)	10.0 mg
Light Technical		Product Data	
Color Code	57	Order product name	FB40DX/6 12PK
Luminous Flux	2,250 lm	Full product name	FB40DX/6 12PK
Color Designation	Daylight Deluxe	Order code	927862005704
Correlated Color Temperature (Nom)	6500 K	Material Nr. (12NC)	927862005704
Color rendering index (CRI)	90	Numerator - Quantity Per Pack	1
Operating and Electrical		EAN/UPC - Product/Case	046677219932
Power Consumption	40 W	Numerator - Packs per outer box	12
		EAN/UPC - Case	50046677219937
Mechanical and Housing			
Bulb Shape	T12-6U [U-bent T 12/8 inch with 6" spacing]		
Net Weight (Piece)	0.300 kg		

## U-Bent Rapid Start T12

### Dimensional drawing

**Product**

FB40DX/6 12PK

