



TL-D Standard Colours

TLDRS16W-CO-25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information		Controls and Dimming	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	Yes
Life to 50% Failures (Nom)	8,000 hour(s)		
Light Technical		Mechanical and Housing	
Color Code	33-640	Bulb Shape	T8
Luminous Flux	1,070 lm	Net Weight (Piece)	70.800 g
Color Designation	Cool White (CW)		
Correlated Color Temperature (Nom)	4100 K	Approval and Application	
Color rendering index (CRI)	63	Mercury (Hg) Content (Nom)	8.0 mg
Operating and Electrical		Product Data	
Power Consumption	16 W	Order product name	TLDRS16W-CO-25
Lamp Current (Nom)	0.265 A	Full product name	TLDRS16W-CO-25
Voltage (Nom)	70 V	Full product code	872790091577800
		Order code	927869003301
		Material Nr. (12NC)	927869003301
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8727900915778

TL-D Standard Colours

Numerator - Packs per outer box	25
EAN/UPC - Case	8727900915785

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TLDRS16W-CO-25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

