



# MASTER TL-D Super 80

## TLDRS32W-S83ECO 25PK

The MASTER TL-D Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)

  

Light Technical	
Color Code	TL830 [CCT of 3000K (830)]
Luminous Flux	2,600 lm
Color Designation	TL830
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	78

  

Operating and Electrical	
Power Consumption	32 W

  

Mechanical and Housing	
Bulb Shape	T-8

  

Net Weight (Piece)	134.400 g
--------------------	-----------

  

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	1.7 mg

  

Product Data	
Order product name	TLDRS32W-S83ECO 25PK
Full product name	TLDRS32W-S83ECO 25PK
Full product code	872790091775800
Order code	927869773002
Material Nr. (12NC)	927869773002
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900917758
Numerator - Packs per outer box	25
EAN/UPC - Case	8727900917765

# MASTER TL-D Super 80

---

## Dimensional drawing

### Product

TLDRS32W-S83ECO 25PK

