



# TL-D Standard Colours

## TLDRS32W-CO-25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	12,000 hour(s)

Light Technical	
Color Code	33-640
Luminous Flux	2,350 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	60

Operating and Electrical	
Power Consumption	32 W
Lamp Current (Nom)	0.265 A
Voltage (Nom)	139 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T8
Net Weight (Piece)	134.400 g


Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg

Product Data	
Order product name	TLDRS32W-CO-25
Full product name	TLDRS32W-CO-25
Full product code	872790091579200
Order code	927870003301
Material Nr. (12NC)	927870003301
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900915792

## TL-D Standard Colours

Numerator - Packs per outer box	25
EAN/UPC - Case	8727900915808

### Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TLDRS32W-CO-25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

