



Tuff Guard High CRI T8 Lamps

F32T8/TL941/ALTO TG 30PK

Tuff Guard T8 lamps are designed to contain shattered glass particles in case of accidental breakage. Coated lighting is essential to help ensure the welfare of your customers, employees, and operation.

Warnings and Safety

- The lamps must be installed and operating in ambient temperatures below 120°F.
- The lamps cannot be used in fixtures employing defective ballasts, ballasts that have been used longer than their rated life or ballasts that are improperly wired.
- The lamps cannot be used in fixtures where poor pin contact occurs.
- Lamp types and ballast types must be compatible (rapid start lamps with rapid start ballast, etc.).
- Lamps are recommended for open fixtures.

Product data

| General Information | | Voltage (Nom) | | 137 V | |
|------------------------------------|---------------------------------|----------------------------|--------------------------|-------|--|
| Cap-Base | G13 [Medium Bi-Pin Fluorescent] | | | | |
| Features | ALTO® (ALTO) | | | | |
| Light Technical | | Mechanical and Housing | | | |
| Color Code | 940 [CCT of 4000K] | Bulb Finish | Coated glass | | |
| Beam Angle (Nom) | 0 degree(s) | Bulb Shape | T-8 | | |
| Color Designation | 4100 Kelvin | Net Weight (Piece) | 0.001 kg | | |
| Correlated Color Temperature (Nom) | 4100 K | | | | |
| Color rendering index (CRI) | >90 | Approval and Application | | | |
| | | Mercury (Hg) Content (Nom) | 1.7 mg | | |
| Operating and Electrical | | Product Data | | | |
| Lamp Current (Nom) | 265 mA | Order product name | F32T8/TL941/ALTO TG 30PK | | |
| Wattage Equivalent | 32 W | Full product name | F32T8/TL941/ALTO TG 30PK | | |
| | | Order code | 927871203913 | | |

Tuff Guard High CRI T8 Lamps

| | |
|---------------------------------|--------------|
| Material Nr. (12NC) | 927871203913 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677536503 |
| Numerator - Packs per outer box | 30 |

| | |
|----------------|----------------|
| EAN/UPC - Case | 50046677536508 |
|----------------|----------------|

Dimensional drawing

| Product | C (max) | D (max) |
|--------------------------|------------|---------|
| F32T8/TL941/ALTO TG 30PK | 1,213.6 mm | 27.9 mm |

