



# High Output T8

## F96T8/D - 6500K 25PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

### Product data

General Information	
Cap-Base	FA8
Light Technical	
Color Code	765 [CCT of 6500K]
Luminous Flux	3,900 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	73
Operating and Electrical	
Power Consumption	60 W
Mechanical and Housing	
Bulb Shape	T-8
Net Weight (Piece)	0.335 kg

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Max)	4.4 mg
Product Data	
Order product name	F96T8/D - 6500K 25PK
Full product name	F96T8/D - 6500K 25PK
Order code	927874705401
Material Nr. (12NC)	927874705401
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677466626
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677466621

# High Output T8

## Dimensional drawing

**Product**

F96T8/D - 6500K 25PK

