



T8 Slimline

F96T8/TL865/ALTO 60W 25PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Warnings and Safety

- Lamp contains mercury.
- Manage in accord with disposal laws.

Product data

General Information	
Cap-Base	FA8
Life to 50% Failures (Nom)	15,000 hour(s)
Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	5,365 lm
Color Designation	6500 Kelvin
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	>81
Operating and Electrical	
Power Consumption	60 W
Mechanical and Housing	
Bulb Finish	Coated glass
Bulb Shape	T-8

Net Weight (Piece)	0.335 kg
Approval and Application	
Mercury (Hg) Content (Nom)	4.4 mg
Product Data	
Order product name	F96T8/TL865/ALTO 60W 25PK
Full product name	F96T8/TL865/ALTO 60W 25PK
Order code	927874786501
Material Nr. (12NC)	927874786501
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677427023
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677427028

T8 Slimline

Dimensional drawing

Product

F96T8/TL865/ALTO 60W 25PK

