



Rapid Start T12

F30T12/CW/RS ALTO 30PK

Philips T12 fluorescent lamps provide high performance and long life in a wide range of sizes, shapes, and types.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Light Technical	
Color Code	33
Luminous Flux	2,250 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	62
Operating and Electrical	
Power Consumption	30 W
Mechanical and Housing	
Bulb Shape	T-12
Net Weight (Piece)	0.163 kg

Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	3.5 mg
Product Data	
Order product name	F30T12/CW/RS ALTO 30PK
Full product name	F30T12/CW/RS ALTO 30PK
Order code	927886003305
Material Nr. (12NC)	927886003305
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677272425
Numerator - Packs per outer box	30
EAN/UPC - Case	50046677272420

Rapid Start T12

Dimensional drawing

Product

F30T12/CW/RS ALTO 30PK

