



TuffGuard Coated T12

F40T12/CWSupreme/ALTO TG

When you select Philips TuffGuard™ Fluorescent lamp with ALTO® lamp technology, you are reducing the impact on the environment, while the coating helps to protect your customers, employees, and reputation. Philips TuffGuard™ fluorescent lamps meet sustainability requirements because they reduce the impact on the environment with low mercury, energy efficiency and long life. The patented green endcaps mean you're using ALTO low-mercury technology. The 16 mils thick coating on TuffGuard™ fluorescent lamps forms a protective seal from end to end and is guaranteed to last the average rated life of the lamp under specific conditions

Warnings and Safety

- All HO lamps recommended for use only in open fixtures.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)

Light Technical	
Luminous Flux	2,600 lm
Color Designation	Cool White Supreme
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	89

Operating and Electrical	
Power Consumption	40 W

Mechanical and Housing	
Bulb Shape	T-12
Net Weight (Piece)	0.001 kg

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	4.4 mg

Product Data	
Order product name	F40T12/CWSupreme/ALTO TG
Full product name	F40T12/CWSupreme/ALTO TG
Order code	927887803902
Material Nr. (12NC)	927887803902
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677424008
Numerator - Packs per outer box	30
EAN/UPC - Case	50046677424003

TuffGuard Coated T12

Dimensional drawing

Product

F40T12/CWSupreme/ALTO TG

