



Rapid Start T12

F40DX ALTO 30PK

Philips T12 fluorescent lamps provide high performance and long life in a wide range of sizes, shapes, and types.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Light Technical	
Color Code	57
Luminous Flux	2,325 lm
Color Designation	Daylight Deluxe
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	90
Operating and Electrical	
Power Consumption	40 W
Mechanical and Housing	
Bulb Shape	T-12
Net Weight (Piece)	0.230 kg

Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	4.4 mg
Product Data	
Order product name	F40DX ALTO 30PK
Full product name	F40DX ALTO 30PK
Order code	927888005709
Material Nr. (12NC)	927888005709
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677273590
Numerator - Packs per outer box	30
EAN/UPC - Case	50046677273595

Rapid Start T12

Dimensional drawing

Product
F40DX ALTO 30PK

