



High Output T12

F48T12/CW/HO ALTO 15PK

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

Product data

General Information	
Cap-Base	R17d (RDC)
Features	ALTO® (ALTO)
Light Technical	
Color Code	33
Luminous Flux	4,050 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	62
Operating and Electrical	
Power Consumption	60 W
Mechanical and Housing	
Bulb Shape	T-12
Net Weight (Piece)	0.223 kg


Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	3.5 mg
Product Data	
Order product name	F48T12/CW/HO ALTO 15PK
Full product name	F48T12/CW/HO ALTO 15PK
Order code	927890203305
Material Nr. (12NC)	927890203305
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677369781
Numerator - Packs per outer box	15
EAN/UPC - Case	50046677369786

High Output T12

Dimensional drawing

Product

F48T12/CW/HO ALTO 15PK



T12 Recessed Double Contact

