



# High Output T12

## F48T12/D/HO ALTO 15PK

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

### Product data

General Information	
Cap-Base	R17d (RDC)
Features	ALTO® (ALTO)
Light Technical	
Color Code	54
Luminous Flux	3,400 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	79
Operating and Electrical	
Power Consumption	60 W
Mechanical and Housing	
Bulb Shape	T-12
Net Weight (Piece)	0.223 kg


Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	3.5 mg
Product Data	
Order product name	F48T12/D/HO ALTO 15PK
Full product name	F48T12/D/HO ALTO 15PK
Order code	927890205402
Material Nr. (12NC)	927890205402
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677369842
Numerator - Packs per outer box	15
EAN/UPC - Case	50046677369847

# High Output T12

## Dimensional drawing

### Product

F48T12/D/HO ALTO 15PK



T12 Recessed Double Contact

