



# High CRI T12

## F96T12/C50Supreme/ALTO 15pk

Philips T12 High CRI Lamps are energy-efficient lighting solutions and provide excellent color consistency over the life of the lamp.

### Product data

| General Information                |              |
|------------------------------------|--------------|
| Cap-Base                           | FA8          |
| Features                           | ALTO® (ALTO) |
| Light Technical                    |              |
| Luminous Flux                      | 5,000 lm     |
| Color Designation                  | C50 Supreme  |
| Correlated Color Temperature (Nom) | 5000 K       |
| Color rendering index (CRI)        | 90           |
| Operating and Electrical           |              |
| Power Consumption                  | 75 W         |
| Mechanical and Housing             |              |
| Bulb Shape                         | T-12         |
| Net Weight (Piece)                 | 0.442 kg     |

| Approval and Application        |                             |
|---------------------------------|-----------------------------|
| Energy Saving Product           | Energy Saving               |
| Mercury (Hg) Content (Nom)      | 6.8 mg                      |
| Product Data                    |                             |
| Order product name              | F96T12/C50Supreme/ALTO 15pk |
| Full product name               | F96T12/C50Supreme/ALTO 15pk |
| Order code                      | 927895000211                |
| Material Nr. (12NC)             | 927895000211                |
| Numerator - Quantity Per Pack   | 1                           |
| EAN/UPC - Product/Case          | 046677423872                |
| Numerator - Packs per outer box | 15                          |
| EAN/UPC - Case                  | 50046677423877              |

## High CRI T12

### Dimensional drawing

**Product**

F96T12/C50Supreme/ALTO 15pk

