



High Output T12

F96T12/DX ALTO 15PK

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

Product data

| General Information | |
|------------------------------------|-----------------|
| Cap-Base | FA8 |
| Features | ALTO® (ALTO) |
| Light Technical | |
| Color Code | 57 |
| Luminous Flux | 4,775 lm |
| Color Designation | Daylight Deluxe |
| Correlated Color Temperature (Nom) | 6500 K |
| Color rendering index (CRI) | 90 |
| Operating and Electrical | |
| Power Consumption | 75 W |
| Mechanical and Housing | |
| Bulb Shape | T-12 |
| Net Weight (Piece) | 0.442 kg |

| Approval and Application | |
|---------------------------------|---------------------|
| Energy Saving Product | Not Applicable |
| Mercury (Hg) Content (Nom) | 6.8 mg |
| Product Data | |
| Order product name | F96T12/DX ALTO 15PK |
| Full product name | F96T12/DX ALTO 15PK |
| Order code | 927895005711 |
| Material Nr. (12NC) | 927895005711 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677372828 |
| Numerator - Packs per outer box | 15 |
| EAN/UPC - Case | 50046677372823 |

High Output T12

Dimensional drawing

Product

F96T12/DX ALTO 15PK

