MASTER PL-L 4 Pin

MASTER PL-L 18W/865/4P 1CT/25

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 2 parallel fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	2G11
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	15,000 hour(s)

Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	1,170 lm
Color Designation	Cool Daylight
Chromaticity Coordinate X (Nom)	0.313
Chromaticity Coordinate Y (Nom)	0.337
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	65 lm/W
Color rendering index (CRI)	80

Operating and Electrical	
Power Consumption	18.0 W
Lamp Current (Nom)	0.375 A

Controls and Dimming	
Dimmable	Yes

MASTER PL-L 4 Pin

Mechanical and Housing	
Net Weight (Piece)	60.900 g

Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	2 mg
Mercury (Hg) Content (Nom)	2.0 mg
Energy Consumption kWh/1000 h	18 kWh
EPREL Registration Number	423264

Product Data	
Order product name	MASTER PL-L 18W/865/4P 1CT/25

Full product name	MASTER PL-L 18W/865/4P 1CT/25
Full product code	871150063514340
Order code	927903086572
Material Nr. (12NC)	927903086572
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500635143
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500635150

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 18W/865/4P 1CT/25	39.0 mm	18.0 mm	194.2 mm	220 mm	226.6 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-L 18W/865/4P 1CT/25

MASTER PL-L 4 Pin

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.