



TUV PL-L

TUV PL-L 24W/4P 1CT/25

TUV PL-L lamps are compact UV-C lamps emitting a peak at 253.7 nm. The compact size of the lamp allows for a small system design and design flexibility. TUV PL-L lamps offer almost constant UV output over their complete lifetime. Thanks to the single-ended lamp base, lamp replacement is easy.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- Plants and/or materials that are exposed to UV-C and/or ozone for a long time may become damaged and/or discolored.

Product data


General Information		Mechanical and Housing	
Cap-Base	2G11	Net Weight (Piece)	82.000 g
Useful Life (Nom)	9,000 hour(s)		
Light Technical		Approval and Application	
Depreciation at Useful Lifetime	20 %	Mercury (Hg) Content (Nom)	4.4 mg
Operating and Electrical		UV	
Power Consumption	24 W	UV-C Radiation at 100 hr	7.6 W
Lamp Current (Nom)	0.345 A		
Voltage (Nom)	87 V	Product Data	
		Order product name	TUV PL-L 24W/4P 1CT/25
		Full product name	TUV PL-L 24W/4P 1CT/25
		Full product code	871829121248500
		Order code	927903204007

TUV PL-L

Material Nr. (12NC)	927903204007
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291212485
Numerator - Packs per outer box	25


EAN/UPC - Case	8718291212492
----------------	---------------

Dimensional drawing



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
TUV PL-L 24W/4P 1CT/25	18 mm	39 mm	290 mm	315 mm	320 mm

Photometric data



Spectral Power Distribution Colour - TUV PL-L 24W/4P 1CT/25

