



PL-L Long 4-Pin Base

PL-L 24W/830/4P 1CT/25

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.


Product data

General Information	
Cap-Base	2G11
Life to 50% Failures (Nom)	15,000 hour(s)
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	1,800 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	75 lm/W
Color rendering index (CRI)	>80
Operating and Electrical	
Power Consumption	24.0 W
Lamp Current (Nom)	0.345 A
Voltage (Nom)	87 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Silicon
Net Weight (Piece)	82.000 g
Product Data	
Order product name	PL-L 24W/830/4P 1CT/25
Full product name	PL-L 24W/830/4P 1CT/25
Order code	927903308321
Material Nr. (12NC)	927903308321
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677345051
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677345056


PL-L Long 4-Pin Base

Dimensional drawing



Product	D (max)	D1 (max)	C (max)
PL-L 24W/830/4P 1CT/25	39.0 mm	18.0 mm	321.6 mm

Photometric data



Spectral Power Distribution Colour - PL-L 24W/830/4P 1CT/25

