



MASTER PL-L 4 Pin

MASTER PL-L 36W/830/4P 1CT/25

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 2 parallel fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	2G11
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	15,000 hour(s)

Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	2,850 lm
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.44
Chromaticity Coordinate Y (Nom)	0.403
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	81 lm/W
Color rendering index (CRI)	82

Operating and Electrical	
Power Consumption	36.3 W

Lamp Current (Nom)	0.435 A
--------------------	---------

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Net Weight (Piece)	104.000 g

Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	2 mg
Mercury (Hg) Content (Nom)	2.0 mg
Energy Consumption kWh/1000 h	37 kWh
EPREL Registration Number	423270


Product Data	
Order product name	MASTER PL-L 36W/830/4P 1CT/25

MASTER PL-L 4 Pin

Full product name	MASTER PL-L 36W/830/4P 1CT/25
Full product code	871150070674440
Order code	927903408370
Material Nr. (12NC)	927903408370
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8711500706744
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500710888

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 36W/830/4P 1CT/25	39.0 mm	18.0 mm	384.2 mm	410 mm	416.6 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-L 36W/830/4P 1CT/25

