



# PL-L Long 4-Pin Base

## PL-L 36W/841/4P 1CT/25

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

### Product data

General Information	
Cap-Base	2G11
Life to 50% Failures (Nom)	15,000 hour(s)

Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	2,900 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	80 lm/W
Color rendering index (CRI)	82

Operating and Electrical	
Power Consumption	36.0 W
Lamp Current (Nom)	0.435 A
Voltage (Nom)	106 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Finish	Silicon
Net Weight (Piece)	104.000 g

Product Data	
Order product name	PL-L 36W/841/4P 1CT/25
Full product name	PL-L 36W/841/4P 1CT/25
Order code	927904508421
Material Nr. (12NC)	927904508421
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677345136
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677345131


# PL-L Long 4-Pin Base

## Dimensional drawing



Product	D (max)	D1 (max)	C (max)
PL-L 36W/841/4P 1CT/25	39.0 mm	18.0 mm	416.6 mm

## Photometric data



Spectral Power Distribution Colour - PL-L 36W/841/4P 1CT/25

