



MASTER PL-L 4 Pin

55 W 4 Pin Cool daylight Non integrated compact fluorescent

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 2 parallel fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Controls and Dimming	
Cap-Base	2G11	Dimmable	Yes
Nominal lifetime	15,000 hour(s)		
Light Technical		Mechanical and Housing	
Color Code	865 [CCT of 6500K]	Net Weight (Piece)	134.000 g
Luminous Flux	4,600 lm		
Color Designation	Cool Daylight	Approval and Application	
Correlated Color Temperature (Nom)	6500 K	Mercury (Hg) Content (Nom)	2.0 mg
Luminous Efficacy (rated) (Nom)	82 lm/W	Energy Consumption kWh/1000 h	61 kWh
Color rendering index (CRI)	80		
Operating and Electrical		Product Data	
Power Consumption	55.0 W	Order product name	55 W 4 Pin Cool daylight Non integrated compact fluorescent
Lamp Current (Nom)	0.525 A	Full product name	55 W 4 Pin Cool daylight Non integrated compact fluorescent
		Full product code	871150026170041

MASTER PL-L 4 Pin

Order code	927908786572
Material Nr. (12NC)	927908786572
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500261700


Numerator - Packs per outer box	25
EAN/UPC - Case	8711500261717

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
55 W 4 Pin Cool daylight Non integrated compact fluorescent	39.0 mm	18.0 mm	509.2 mm	535 mm	541.6 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-L 55W/865/4P 1CT/25

