



# PL-T Triple 4-Pin Base

## PL-T 32W/841/A/4P 1CT/5X10BOX ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

### Product data

General Information	
Cap-Base	GX24q-3

Light Technical	
Color Code	841 [CCT of 4100K]
Luminous Flux	2,250 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	68.2 lm/W
Color rendering index (CRI)	80

Operating and Electrical	
Power Consumption	32 W
Lamp Current (Nom)	0.320 A

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Net Weight (Piece)	70.000 g


Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg

Product Data	
Order product name	PL-T 32W/841/A/4P 1CT/5X10BOX ALTO
Full product name	PL-T 32W/841/A/4P 1CT/5X10BOX ALTO
Order code	927911084150
Material Nr. (12NC)	927911084150
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677268725
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677458312



# PL-T Triple 4-Pin Base

## Dimensional drawing




Product	D (max)	A (max)	B (max)	C (max)
PL-T 32W/841/A/4P 1CT/5X10BOX ALTO	41 mm	98.7 mm	123.0 mm	138.7 mm

## Lifetime



Lumen Maintenance Diagram - PL-T 32W/841/A/4P 1CT/5X10BOX ALTO

Life expectancy diagram - 3 hour cycle



Life expectancy diagram - 12 hour cycle

## PL-T Triple 4-Pin Base

