

PHILIPS

Lighting



# MASTER TL-D Super 80 日光燈管

## MASTER TL-D Super 80 38W/830 SLV/25

直徑 26 mm 的螢光燈管

### 安全提示

· A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### 产品数据

一般資訊		控制與調光	
燈座基底	G13 [Medium Bi-Pin Fluorescent]	可調光	是
測量測量參考	Sphere		
壽命 (故障率 50%) (標稱)	15,000 h		
照明技術		機械與外罩	
色碼	830 [CCT of 3000K]	燈泡形狀	T8
光通量	3,300 lm	淨重 (個)	133.000 g
色彩名稱	暖白光 (WW)		
色度坐標 X (標稱)	0.44	認證與應用	
色度坐標 Y (Nom)	0.403	節能等級	G
相關色溫 (標稱)	3000 K	汞 (Hg) 含量 (標稱)	1.7 mg
光效 (額定) (標準)	88 lm/W	能源消耗 kWh/1000 h	39 kWh
演色性指數 (CRI)	82	EPREL 註冊碼	423432
運轉與電力		產品資料	
耗電量	38.2 W	下訂產品名稱	MASTER TL-D Super 80 38W/830 SLV/25
燈具電流 (標稱)	0.430 A	完整產品名稱	MASTER TL-D Super 80 38W/830 SLV/25
		完整產品代碼	871150055880040
		訂單代碼	927923583014
		材質 Nr. (12NC)	927923583014


# MASTER TL-D Super 80 日光燈管

分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500558800
分子 - 每一外盒包裝	25


EAN/UPC - 箱	8711500558817
-------------	---------------

## 二维绘图

Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Super 80 38W/830 SLV/25	28 mm	1,047.0 mm	1,054.1 mm	1,051.7 mm	1,061.2 mm




## 光度数据




Spectral Power Distribution Colour - MASTER TL-D Super 80 38W/830 SLV/25

## 壽命




Life expectancy diagram - 3 hour cycle



Life expectancy diagram - 12 hour cycle

# MASTER TL-D Super 80 日光燈管

## 壽命



Lumen Maintenance Diagram - MASTER TL-D Super 80 38W/830 SLV/25

