



TUV T8

TUV T8 F17 1SL/25

TUV T8 lamps are double-ended UVC (germicidal) lamps used in professional water and air disinfection units. TUV T8 lamps offer almost constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Moreover, they have a long and reliable lifetime, which allows maintenance to be planned for in advance.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

Product data


General Information		Mechanical and Housing	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Net Weight (Piece)	100.000 g
Useful Life (Nom)	9,000 hour(s)		
Light Technical		Approval and Application	
Depreciation at Useful Lifetime	15 %	Mercury (Hg) Content (Nom)	5.0 mg
		CE mark	Yes
Operating and Electrical		UV	
Power Consumption	16.7 W	UV-C Radiation at 100 hr	6 W
Lamp Current (Nom)	0.236 A		
Voltage (Nom)	72 V		
Product Data			
Order product name	TUV T8 F17 1SL/25		
Full product name	TUV T8 F17 1SL/25		
Full product code	871150026413840		

TUV T8

Order code	26413840
Material Nr. (12NC)	927941904020
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500264138

Numerator - Packs per outer box	25
EAN/UPC - Case	8711500264145

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TUV T8 F17 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604.0 mm

Photometric data



Spectral Power Distribution Colour - TUV T8 F17 1SL/25

