



# TL Mini Standard Colours



## TL Mini EL 4W/33-640 FAM/10X25BOX

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Voltage (Nom)	
Cap-Base	G5	29 V	
Flux measurement reference	Sphere	Controls and Dimming	
Life to 50% Failures (Nom)	10,000 hour(s)	Dimmable	Yes
Light Technical		Mechanical and Housing	
Color Code	33-640	Bulb Shape	T5
Luminous Flux	130 lm	Net Weight (Piece)	14.000 g
Color Designation	Cool White (CW)	Approval and Application	
Chromaticity Coordinate X (Nom)	0.38	Energy Efficiency Class	G
Chromaticity Coordinate Y (Nom)	0.38	Mercury (Hg) Content (Max)	2.5 mg
Correlated Color Temperature (Nom)	4000 K	Mercury (Hg) Content (Nom)	4.4 mg
Luminous Efficacy (rated) (Nom)	35 lm/W	Energy Consumption kWh/1000 h	5 kWh
Color rendering index (CRI)	58	EPREL Registration Number	423486
Operating and Electrical		Product Data	
Power Consumption	4.5 W	Order product name	TL Mini EL 4W/33-640 FAM/10X25BOX
Lamp Current (Nom)	0.170 A	Full product name	TL Mini EL 4W/33-640 FAM/10X25BOX

## TL Mini Standard Colours

Full product code	871150061568827
Order code	61568827
Material Nr. (12NC)	928000003340
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500615688


Numerator - Packs per outer box	250
EAN/UPC - Case	8711500615701

### Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL Mini EL 4W/33-640 FAM/10X25BOX	16 mm	135.9 mm	143.0 mm	140.6 mm	150.1 mm

### Photometric data



Spectral Power Distribution Colour - TL Mini EL 4W/33-640 FAM/10X25BOX

