



Product Description

TUV TL Mini lamps are slim double-ended UVC (germicidal) lamps used in residential water and air disinfection units. The small 16 mm diameter of the lamp allows for a small system design and design flexibility. TUV TL Mini lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

General Information

Cap-Base	G5
Useful Life (Nom)	6,000 h

Light Technical

Depreciation at Useful Lifetime	25 %
---------------------------------	------

Operating and Electrical

Power Consumption	4.5 W
Lamp Current (Nom)	0.17 A
Voltage (Nom)	29 V

Mechanical and Housing

Net Weight (Piece)	18.600 g
--------------------	----------

Approval and Application

Mercury (Hg) Content (Nom)	4.4 mg
CE mark	Yes

UV


UV-C Radiation at 100 hr	0.9 W
--------------------------	-------

Product Data

Order product name	TUV 4W FAM/10X25BOX
Full product name	TUV 4W FAM/10X25BOX
Full product code	871150063872427
Order code	928000104013


Material Nr. (12NC)	928000104013
Local order code	TUV4W
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500638724
Numerator - Packs per outer box	250
EAN/UPC - Case	8711500638748

Dimensional drawing



Product	D	C
TUV 4W FAM/10X25BOX	16 mm	150.1 mm

Photometric data



Spectral Power Distribution Colour - TUV 4W FAM/10X25BOX

