



TL Mini Standard Colours



TL Mini EL 6W/33-640 FAM/10X25BOX

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G5
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	10,000 hour(s)

Light Technical	
Color Code	33-640
Luminous Flux	260 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	43 lm/W
Color rendering index (CRI)	59

Operating and Electrical	
Power Consumption	6.0 W
Lamp Current (Nom)	0.160 A

Voltage (Nom)	42 V
---------------	------

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T5
Net Weight (Piece)	21.000 g

Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	2.5 mg
Mercury (Hg) Content (Nom)	4.4 mg
Energy Consumption kWh/1000 h	6 kWh
EPREL Registration Number	423488


Product Data	
Order product name	TL Mini EL 6W/33-640 FAM/10X25BOX
Full product name	TL Mini EL 6W/33-640 FAM/10X25BOX

TL Mini Standard Colours

Full product code	871150071583827
Order code	71583827
Material Nr. (12NC)	928000503340
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500715838


Numerator - Packs per outer box	250
EAN/UPC - Case	8711500715852

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL Mini EL 6W/33-640 FAM/ 10X25BOX	16 mm	212.1 mm	219.2 mm	216.8 mm	226.3 mm

Photometric data



Spectral Power Distribution Colour - TL Mini EL 6W/33-640 FAM/10X25BOX

