

Actinic BL TL 11W/10

928000601030



Actinic BL TL(-K)/TL-D(-K) – optimized for Electronic Fly Killers

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

General Information

Cap-Base	G5
Useful Life (Nom)	2,000 hour(s)

Light Technical

Color Code	10
Color Designation	Actinic
Chromaticity Coordinate X (Nom)	230
Chromaticity Coordinate Y (Nom)	230
UV Depreciation at 1000 h	40 %
UV Depreciation at 2000 h	45 %
UV Depreciation at 500 h	30 %

Operating and Electrical

Power Consumption	11.5 W
Lamp Current (Nom)	0.400 A
Voltage (Nom)	34 V

Mechanical and Housing

Bulb Shape	T16
Net Weight (Piece)	21.000 g


Approval and Application

Mercury (Hg) Content (Nom)	4.4 mg
CE mark	Yes

UV


UV-A Radiation 100Hr (IEC)	2.0 W
----------------------------	-------

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL 11W/10	16 mm	212.1 mm	219.2 mm	216.8 mm	226.3 mm

Photometric data



Spectral Power Distribution Colour - Actinic BL TL 11W/10

Product Data

Order product name	Actinic BL TL 11W/10
Full product name	Actinic BL TL 11W/10
Full product code	871150095145827
Order code	95145827
Material Nr. (12NC)	928000601030
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500951458
Numerator - Packs per outer box	250
EAN/UPC - Case	8711500951472

