



# T5 Preheat

## F8T5/CW PH 25PK

Philips T5 Fluorescent Lamps are incredibly powerful, environmentally responsible, long life lamps with an ultra-slim profile. This translates into reduced maintenance and disposal costs and also allows the use of smaller fixtures—which reduces ceiling clutter.

### Product data


General Information	
Cap-Base	G5
Life to 50% Failures (Nom)	10,000 hour(s)
Light Technical	
Color Code	33-640
Luminous Flux	410 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	51 lm/W
Color rendering index (CRI)	60
Operating and Electrical	
Power Consumption	7.1 W
Lamp Current (Nom)	0.145 A
Voltage (Nom)	56 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T5
Net Weight (Piece)	27.000 g
Approval and Application	
Mercury (Hg) Content (Nom)	4.4 mg
Energy Consumption kWh/1000 h	8 kWh
Product Data	
Order product name	F8T5/CW PH 25PK
Full product name	F8T5/CW PH 25PK
Order code	928001003321
Material Nr. (12NC)	928001003321
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677114640
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677114645


# T5 Preheat

## Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
F8T5/CW PH 25PK	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm



## Photometric data



Spectral Power Distribution Colour - F8T5/CW PH 25PK

