



TUV TL Mini - Small diameter lamps for residential applications

TUV TL Mini lamps are slim double-ended UVC (germicidal) lamps used in residential water and air disinfection units. The small 16 mm diameter of the lamp allows for a small system design and design flexibility. TUV TL Mini lamps offer almost constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

General Information

Cap-Base	G5
Useful Life (Nom)	9,000 hour(s)

Light Technical

Color Code	TUV
Color Designation	- [Not Specified]
Depreciation at Useful Lifetime	15 %

Operating and Electrical

Power Consumption	7.1 W
Lamp Current (Nom)	0.145 A
Voltage (Nom)	56 V

Mechanical and Housing

Bulb Shape	T16
Net Weight (Piece)	24.810 g

Approval and Application

Mercury (Hg) Content (Nom)	4.4 mg
----------------------------	--------


UV

UV-C Radiation at 100 hr	2.5 W
--------------------------	-------

Product Data


Order product name	TUV 8W IN FAM/10X25BOX
Full product name	TUV 8W IN FAM/10X25BOX
Full product code	871951432789400
Order code	928001104021
Material Nr. (12NC)	928001104021
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514327894
Numerator - Packs per outer box	250
EAN/UPC - Case	8719514327917

Dimensional drawing



Product	D	C
TUV 8W IN FAM/10X25BOX	16 mm	302.5 mm

Photometric data



Spectral Power Distribution Colour - TUV 8W IN FAM/10X25BOX

