



Actinic BL TL(-K) / TL-D(-K)

Actinic BL TL MINI 15W/10 /10X25CC

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G5
Light Technical	
Color Code	10
Color Designation	Actinic
UV Depreciation at 1000 h	40 %
UV Depreciation at 2000 h	45 %
UV Depreciation at 500 h	30 %
Operating and Electrical	
Power Consumption	15 W
Lamp Current (Nom)	0.40 A


Voltage (Nom)	43 V
Mechanical and Housing	
Bulb Shape	T16
Net Weight (Piece)	25.300 g
UV	
UV-A Radiation 100Hr (IEC)	3 W
Product Data	
Order product name	Actinic BL TL MINI 15W/10 /10X25CC
Full product name	Actinic BL TL MINI 15W/10 /10X25CC
Full product code	871150095148927

Actinic BL TL(-K) / TL-D(-K)

Order code	928001201030
Material Nr. (12NC)	928001201030
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500951489


Numerator - Packs per outer box	250
EAN/UPC - Case	8711500951502

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL MINI 15W/10 / 10X25CC	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm

Photometric data



Spectral Power Distribution Colour - Actinic BL TL MINI 15W/10 /10X25CC

