



T5 Preheat

F13T5/CW PH 25PK

Philips T5 Fluorescent Lamps are incredibly powerful, environmentally responsible, long life lamps with an ultra-slim profile. This translates into reduced maintenance and disposal costs and also allows the use of smaller fixtures—which reduces ceiling clutter.

Product data


General Information	
Cap-Base	G5
Life to 50% Failures (Nom)	8,000 hour(s)
Light Technical	
Color Code	33-640
Luminous Flux	930 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	71 lm/W
Color rendering index (CRI)	60
Operating and Electrical	
Power Consumption	13.0 W
Lamp Current (Nom)	0.170 A
Voltage (Nom)	90 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T5
Net Weight (Piece)	40.200 g
Approval and Application	
Mercury (Hg) Content (Nom)	4.4 mg
Energy Consumption kWh/1000 h	14 kWh
Product Data	
Order product name	F13T5/CW PH 25PK
Full product name	F13T5/CW PH 25PK
Order code	928001503332
Material Nr. (12NC)	928001503332
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677115142
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677115147


T5 Preheat

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
F13T5/CW PH 25PK	16 mm	516.9 mm	524.0 mm	521.6 mm	531.1 mm



Photometric data



Spectral Power Distribution Colour - F13T5/CW PH 25PK

