



TL Mini Standard Colours



TL Mini EL 13W/33-640 FAM/10X25BOX

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G5
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	8,000 hour(s)

Light Technical	
Color Code	33-640
Luminous Flux	835 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	71 lm/W
Color rendering index (CRI)	59

Operating and Electrical	
Power Consumption	13.1 W
Lamp Current (Nom)	0.170 A

Voltage (Nom)	
Voltage (Nom)	90 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T5
Net Weight (Piece)	50.340 g

Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	2.5 mg
Mercury (Hg) Content (Nom)	4.4 mg
Energy Consumption kWh/1000 h	14 kWh
EPREL Registration Number	423498


Product Data	
Order product name	TL Mini EL 13W/33-640 FAM/10X25BOX
Full product name	TL Mini EL 13W/33-640 FAM/10X25BOX

TL Mini Standard Colours

Full product code	871150070475727
Order code	70475727
Material Nr. (12NC)	928001503340
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500704757


Numerator - Packs per outer box	250
EAN/UPC - Case	8711500718518

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL Mini EL 13W/33-640 FAM/ 10X25BOX	16 mm	516.9 mm	524.0 mm	521.6 mm	531.1 mm

Photometric data



Spectral Power Distribution Colour - TL Mini EL 13W/33-640 FAM/10X25BOX

