



TUV TL Mini - Small diameter lamps for residential applications

TUV TL Mini lamps are slim double-ended UV-C 253.7 nm emitting lamps. The small 16 mm diameter of the lamp allows for a small system design and design flexibility. TUV TL Mini lamps offer almost constant UV output over their complete lifetime.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- Plants and/or materials that are exposed to UV-C and/or ozone for a long time may become damaged and/or discolored.

General Information

Cap-Base	G5
Useful Life (Nom)	9,000 hour(s)

Light Technical

Depreciation at Useful Lifetime	15 %
---------------------------------	------

Operating and Electrical

Power Consumption	11.5 W
Lamp Current (Nom)	0.4 A
Voltage (Nom)	34 V

Mechanical and Housing

Net Weight (Piece)	22.000 g
--------------------	----------

Approval and Application

Mercury (Hg) Content (Nom)	4.4 mg
CE mark	Yes


UV

UV-C Radiation at 100 hr	2.6 W
--------------------------	-------

Product Data


Order product name	TUV 11W FAM/10X25BOX
Full product name	TUV 11W FAM/10X25BOX
Full product code	871150055965427
Order code	928002204013
Material Nr. (12NC)	928002204013
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500559654
Numerator - Packs per outer box	250
EAN/UPC - Case	8711500559715

Dimensional drawing



Product	D	C
TUV 11W FAM/10X25BOX	16 mm	226.3 mm

Photometric data



Spectral Power Distribution Colour - TUV 11W FAM/10X25BOX

