



TUV TL Mini

TUV 11W CN FAM/10X25BOX

TUV TL Mini lamps are slim double-ended UV-C 253.7 nm emitting lamps. The small 16 mm diameter of the lamp allows for a small system design and design flexibility. TUV TL Mini lamps offer almost constant UV output over their complete lifetime.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- Plants and/or materials that are exposed to UV-C and/or ozone for a long time may become damaged and/or discolored.

Product data


General Information		Mechanical and Housing	
Cap-Base	G5	Bulb Shape	T16
Useful Life (Nom)	9,000 hour(s)	Net Weight (Piece)	19.570 g
Light Technical		Approval and Application	
Color Code	TUV	Mercury (Hg) Content (Nom)	4.4 mg
Color Designation	- [Not Specified]		
Depreciation at Useful Lifetime	15 %	UV	
Operating and Electrical		UV-C Radiation at 100 hr	2.6 W
Power Consumption	11.5 W	Product Data	
Lamp Current (Nom)	0.4 A	Order product name	TUV 11W CN FAM/10X25BOX
Voltage (Nom)	34 V	Full product name	TUV 11W CN FAM/10X25BOX
		Full product code	692234192429300
		Order code	928002204019

TUV TL Mini

Material Nr. (12NC)	928002204019
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6922341924293
Numerator - Packs per outer box	250

EAN/UPC - Case	6922341924316
----------------	---------------

Dimensional drawing



Product	D	C
TUV 11W CN FAM/10X25BOX	16 mm	226.3 mm

Photometric data



Spectral Power Distribution Colour - TUV 11W CN FAM/10X25BOX

