



TUV TL Mini

TUV 25W FAM/10X25BOX

TUV TL Mini lamps are slim double-ended UVC (germicidal) lamps used in residential water and air disinfection units. The small 16 mm diameter of the lamp allows for a small system design and design flexibility. TUV TL Mini lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

Product data

General Information	
Cap-Base	G5
Useful Life (Nom)	9,000 hour(s)
Light Technical	
Depreciation at Useful Lifetime	20 %
Operating and Electrical	
Power Consumption	23 W
Lamp Current (Nom)	0.350 A
Voltage (Nom)	82 V


Mechanical and Housing	
Net Weight (Piece)	40.200 g
Approval and Application	
Mercury (Hg) Content (Nom)	4.4 mg
UV	
UV-C Radiation at 100 hr	8.4 W
Product Data	
Order product name	TUV 25W FAM/10X25BOX
Full product name	TUV 25W FAM/10X25BOX
Full product code	871150088905827
Order code	928002604013

TUV TL Mini

Material Nr. (12NC)	928002604013
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500889058
Numerator - Packs per outer box	250

EAN/UPC - Case	8711500889072
----------------	---------------

Dimensional drawing



Product	D (max)	C (max)	A (max)
TUV 25W FAM/10X25BOX	16 mm	531.1 mm	

