



Blue (/52) TL/TL-D

TL 20W/52 SLV/25

Tubular or compact single-ended low-pressure mercury vapour fluorescent lamps

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information		Controls and Dimming	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	No
Life to 50% Failures (Nom)	9,000 hour(s)		
Useful Life (Nom)	2,000 hour(s)		
Light Technical		Mechanical and Housing	
Color Code	52	Bulb Shape	T38
Luminous Flux	318 lm	Net Weight (Piece)	156.000 g
Chromaticity Coordinate X (Nom)	154		
Chromaticity Coordinate Y (Nom)	69		
Operating and Electrical		Approval and Application	
Power Consumption	19.3 W	Mercury (Hg) Content (Nom)	8.0 mg
Lamp Current (Nom)	0.36 A	CE mark	Yes
Voltage (Nom)	59 V		
Product Data			
Order product name	TL 20W/52 SLV/25		
Full product name	TL 20W/52 SLV/25		
Full product code	871150064302540		
Order code	928003505203		
Material Nr. (12NC)	928003505203		
Numerator - Quantity Per Pack	1		

Blue (/52) TL/TL-D


EAN/UPC - Product/Case	8711500643025
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500643032

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 20W/52 SLV/25	40.5 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

Photometric data



Spectral Power Distribution Colour - TL 20W/52 SLV/25

