



# T12 Standard

## F20T12/D-765 25 PK


Low-pressure mercury discharge lamps with a tubular 37 mm envelope

### Product data

General Information		Approval and Application	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Mercury (Hg) Content (Nom)	8.0 mg
Life to 50% Failures (Nom)	9,000 hour(s)	<b>Product Data</b>	
<b>Light Technical</b>		Order product name	F20T12/D-765 25 PK
Color Code	54-765	Full product name	F20T12/D-765 25 PK
Luminous Flux	975 lm	Full product code	871869667308900
Color Designation	Cool Daylight	Order code	928003505415
Correlated Color Temperature (Nom)	6200 K	Material Nr. (12NC)	928003505415
Color rendering index (CRI)	72	Numerator - Quantity Per Pack	1
<b>Operating and Electrical</b>		EAN/UPC - Product/Case	8718696673089
Power Consumption	19.3 W	Numerator - Packs per outer box	25
Voltage (Nom)	59 V	EAN/UPC - Case	8718696673096
<b>Controls and Dimming</b>			
Dimmable	Yes		
<b>Mechanical and Housing</b>			
Bulb Shape	T12		


# T12 Standard

## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
F20T12/D-765 25 PK	40.5 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

## Photometric data



Spectral Power Distribution Colour - F20T12/D-765 25 PK

