Flexo Print

TL 80W/10-R SLV/25

Tubular low-pressure mercury vapour discharge lamps

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	1,000 hour(s)
Useful Life (Nom)	1,000 hour(s)

Light Technical	
Color Code	10-R
Color Designation	Ultra Violet A
Chromaticity Coordinate X (Nom)	222
Chromaticity Coordinate Y (Nom)	210
UV Depreciation at 1000 h	20 %
UV Depreciation at 2000 h	30 %
UV Depreciation at 500 h	10 %

Operating and Electrical	
Power Consumption	80 W
Lamp Current (Nom)	0.83 A
Voltage (Nom)	110 V

Mechanical and Housing	
Bulb Shape	T38
Net Weight (Piece)	331.000 g

Approval and Application	
Mercury (Hg) Content (Nom)	13.0 mg
CE mark	Yes

UV	
UV-A Radiation 100Hr (IEC)	19.0 W

Product Data	
Order product name	TL 80W/10-R SLV/25
Full product name	TL 80W/10-R SLV/25
Full product code	871150061262540
Order code	928005901029
Material Nr. (12NC)	928005901029
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500612625
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500612632

Flexo Print

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 80W/10-R SLV/25	40.5 mm	1,500 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm



Photometric data



Spectral Power Distribution Colour - TL 80W/10-R SLV/25

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.