



T12 Standard

F40T12/54-765 1SL/25

Low-pressure mercury discharge lamps with a tubular 37 mm envelope


Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Luminous Flux	2,500 lm
Color Designation	6500 Kelvin
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	72
Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	107 V
Mechanical and Housing	
Bulb Shape	T-12
Net Weight (Piece)	214.000 g

Approval and Application	
Mercury (Hg) Content (Nom)	8 mg
Product Data	
Order product name	F40T12/54-765 1SL/25
Full product name	F40T12/54-765 1SL/25
Full product code	871869966082600
Order code	928006005401
Material Nr. (12NC)	928006005401
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699660826
Numerator - Packs per outer box	25
EAN/UPC - Case	8718699660833

T12 Standard

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
F40T12/54-765 1SL/25	40.5 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

