



T12 Standard

F40T12/D-765 25 PK

Low-pressure mercury discharge lamps with a tubular 37 mm envelope

Product data


General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	54-765
Luminous Flux	2,500 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6200 K
Color rendering index (CRI)	75
Operating and Electrical	
Power Consumption	39.5 W
Voltage (Nom)	107 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T12

Net Weight (Piece)	0.229 kg
Approval and Application	
Mercury (Hg) Content (Nom)	10.5 mg
Product Data	
Order product name	F40T12/D-765 25 PK
Full product name	F40T12/D-765 25 PK
Full product code	871869667310200
Order code	928006405415
Material Nr. (12NC)	928006405415
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696673102
Numerator - Packs per outer box	25
EAN/UPC - Case	8718696673119


T12 Standard

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
F40T12/D-765 25 PK	40.5 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm



Photometric data



Spectral Power Distribution Colour - F40T12/D-765 25 PK

