



Flexo Print

TL 60W/10-R SLV/25

Tubular low-pressure mercury vapour discharge lamps

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	2,000 hour(s)
Useful Life (Nom)	1,000 hour(s)
Light Technical	
Color Code	10-R
Color Designation	Ultra Violet A
Chromaticity Coordinate X (Nom)	222
Chromaticity Coordinate Y (Nom)	210
UV Depreciation at 1000 h	15 %
UV Depreciation at 2000 h	30 %
UV Depreciation at 500 h	10 %
Operating and Electrical	
Power Consumption	62 W
Lamp Current (Nom)	0.7 A
Voltage (Nom)	102 V
Mechanical and Housing	
Bulb Shape	T38

Net Weight (Piece)	260.200 g
Approval and Application	
Mercury (Hg) Content (Nom)	13.0 mg
CE mark	Yes
UV	
UV-A Radiation 100Hr (IEC)	15.8 W
Product Data	
Order product name	TL 60W/10-R SLV/25
Full product name	TL 60W/10-R SLV/25
Full product code	871150061572540
Order code	928008401003
Material Nr. (12NC)	928008401003
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500615725
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500615732


Flexo Print

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 60W/10-R SLV/25	40.5 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm



Photometric data



Spectral Power Distribution Colour - TL 60W/10-R SLV/25

