



# Flexo Print

## TL 140W/03

Tubular low-pressure mercury vapour discharge lamps

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


### Product data

| General Information             |                                 |
|---------------------------------|---------------------------------|
| Cap-Base                        | G13 [Medium Bi-Pin Fluorescent] |
| Life to 50% Failures (Nom)      | 3,000 hour(s)                   |
| Light Technical                 |                                 |
| Color Code                      | 03                              |
| Color Designation               | Super Actinic                   |
| Chromaticity Coordinate X (Nom) | 175                             |
| Chromaticity Coordinate Y (Nom) | 45                              |
| UV Depreciation at 1000 h       | 30 %                            |
| UV Depreciation at 2000 h       | 40 %                            |
| UV Depreciation at 500 h        | 20 %                            |
| Operating and Electrical        |                                 |
| Power Consumption               | 140 W                           |
| Lamp Current (Nom)              | 1.46 A                          |
| Voltage (Nom)                   | 118 V                           |
| Mechanical and Housing          |                                 |
| Bulb Shape                      | T38                             |


| Net Weight (Piece)              | 331.000 g       |
|---------------------------------|-----------------|
| Approval and Application        |                 |
| CE mark                         | Yes             |
| UV                              |                 |
| UV-A Radiation 100Hr (IEC)      | 1.00 W          |
| Product Data                    |                 |
| Order product name              | TL 140W/03      |
| Full product name               | TL 140W/03      |
| Full product code               | 871150072094840 |
| Order code                      | 928012700303    |
| Material Nr. (12NC)             | 928012700303    |
| Numerator - Quantity Per Pack   | 1               |
| EAN/UPC - Product/Case          | 8711500720948   |
| Numerator - Packs per outer box | 25              |
| EAN/UPC - Case                  | 8711500720955   |

Dimensional drawing

| Product    | D (max) | A (max)  | B (max)    | B (min)    | C (max)    |
|------------|---------|----------|------------|------------|------------|
| TL 140W/03 | 40.5 mm | 1,500 mm | 1,507.1 mm | 1,504.7 mm | 1,514.2 mm |



Photometric data



Spectral Power Distribution Colour - TL 140W/03

