



# TUV T8

## TUV T8 10W SL/25

TUV T8 lamps are double-ended UVC (germicidal) lamps used in professional water and air disinfection units. TUV T8 lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Moreover, they have a long and reliable lifetime, which allows maintenance to be planned for in advance.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

### Product data

General Information		Lamp Current (Nom)		0.230 A
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Voltage (Nom)	48 V	
Useful Life (Nom)	9,000 hour(s)	Mechanical and Housing		
Light Technical		Net Weight (Piece)	0.054 kg	
Depreciation at Useful Lifetime	15 %	Approval and Application		
Operating and Electrical		Mercury (Hg) Content (Nom)	4.0 mg	
Power Consumption	9.9 W			


# TUV T8

CE mark	Yes
<b>UV</b>	
UV-C Radiation at 100 hr	2.7 W
<b>Product Data</b>	
Order product name	TUV T8 10W SL/25
Full product name	TUV T8 10W SL/25
Full product code	694793919609800


Order code	928023904011
Material Nr. (12NC)	928023904011
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6947939196098
Numerator - Packs per outer box	25
EAN/UPC - Case	6947939196104

## Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TUV T8 10W SL/25	28 mm	331.5 mm	338.6 mm	336.2 mm	345.7 mm



## Photometric data



Spectral Power Distribution Colour - TUV T8 10W SL/25

