



TL-E 80

22 W G10q Cool daylight Circular fluorescent

Fluorescent lamps with a circular tube having a diameter of 26 mm


Product data

General Information	
Cap-Base	G10q
Nominal lifetime	8,000 hour(s)
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	1,250 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	57 lm/W
Color rendering index (CRI)	80
Operating and Electrical	
Power Consumption	22.0 W
Lamp Current (Nom)	0.400 A
Voltage (Nom)	62 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	C-T29
Net Weight (Piece)	0.110 kg
Approval and Application	
Mercury (Hg) Content (Nom)	8 mg
Energy Consumption kWh/1000 h	24 kWh
Product Data	
Order product name	22 W G10q Cool daylight Circular fluorescent
Full product name	22 W G10q Cool daylight Circular fluorescent
Full product code	871150028667300
Order code	928026286574
Material Nr. (12NC)	928026286574
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500286673
Numerator - Packs per outer box	20
EAN/UPC - Case	8727900813586

TL-E 80

Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
22 W G10q Cool daylight	30.9 mm	26.2 mm	205.0 mm	213.5 mm	149.1 mm	155.6 mm
Circular fluorescent						

